

Connecting HID Maxiprox Reader to Net2


Unit tested: HID Maxiprox
Model: 5375
Card tested:

Date Tested: 19/10/04

Net2 ACU Reader Connections:

Connections from reader to ACU

Reader Cable	ACU Terminal
(2) +DC	- Red
(8) Red LED	- Brown
	- Orange
(7) Green LED	- Green
(4) Data 0	- Yellow
(5) Data 1	- Blue
	- Mauve
(3) Ground	- Black/White



Note: Terminals 1, 6, 9, 10, 11 and 12 are not used. There are also Voltage selection jumpers for 12volts and 24volts.

Additional settings:

To setup the LED configure the Registry as follows:

Run REGEDIT

HKEY_LOCAL_MACHINE → Software → Paxton Access → Access Control

LEDStyle

Modify this value to '1' and reboot the PC, then reinstate the doors from Net2.

LED: Steady Red - Waiting for a card
 Steady Green - Door open
 Flicker - User barred